

The everyday color laser printer that's  
*anything but ordinary.*



**e-STUDIO™ 220cp**

  
24 BW/22 C

  
Workgroup

  
Color

**TOSHIBA**  
Leading Innovation >>>

# e-STUDIO™ 220CP

## SPECIFICATIONS

This exceptional yet affordable color laser printer is perfect for hard-working offices. The e-STUDIO220CP delivers brilliant color quickly and effortlessly, keeping office productivity at its peak. Also, a newly designed operator panel makes color printing easier than ever.



**24/22**  
B&W/Color  
PPM

High speed output of  
24 PPM B&W and 22 PPM Color



Superb 4800  
color quality



Also available with  
a 550-sheet drawer

### SPECIFICATIONS

<b>Engine Technology</b>	Color Laser
<b>Print Speed</b>	Up to 24/22 PPM Black & White/Color 11 Second First-Print-Out
<b>Print Quality</b>	4800 Color Quality 1200 x 1200 dpi Resolution
<b>Memory</b>	128 MB - Standard 640 MB - Maximum
<b>Connectivity</b>	(Standard) 10/100BaseTX Ethernet, USB 2.0 (Optional) 802.11g Wireless Adapter
<b>Compatibility</b>	PostScript™ 3 Emulation PCL5c™ and PCL6™ Emulations PPDS PDF 1.5
<b>Paper Handling</b>	Input Standard/Max - 250/800 Sheets Output Standard/Max - 250/250 Sheets
<b>Media Sizes</b>	Letter, Legal, A4, A5, JIS B5, Executive, Folio, Statement - Standard Tray and Optional Drawer Universal (3" x 6" to 8.5" x 14") - Bypass Envelopes: DL, C5, B5, 7.75, 9, 10 - Bypass
<b>Media Types</b>	Plain Paper, Recycled Paper, Card Stock, Transparencies -Standard Tray and Optional Drawer Envelopes and Paper Labels - Bypass
<b>Media Weights</b>	16 - 47 lb. Long Grain Bond, 24 - 58 lb. Short Grain Bond - Standard Tray and Optional Drawer Up to 100 lb. Card Stock (Tag) - Bypass
<b>Supplies</b>	Ships with 4K Yield Black and 3K Yield Color (C, M, Y) Starter Cartridges Ships With 20K Photoconductor 4K Yield Black Replacement Cartridge - Regular and Use and Return Available 5K Yield Color (C, M, Y) Replacement Cartridges - Regular and Use and Return Available
<b>Operating Systems</b>	Windows® 2000, XP, 2003 Server, Vista Macintosh® OS 9.x, 10.2 or higher
<b>Dimensions</b>	19"(H) x 17.3"(W) x 16.1"(D) 484 mm x 440 mm x 408 mm
<b>Weight</b>	57 lbs. (~26 kg)
<b>Acoustics</b>	51 dBA Color Printing 31 dBA Idle
<b>Maximum Monthly Volume</b>	Up to 75,000 Pages per Month

### ACCESSORIES

<b>36B1600</b>	550 Sheet Drawer
<b>14T0145</b>	Wireless Print Server
<b>13N1523</b>	128 MB Memory
<b>13N1524</b>	256 MB Memory
<b>13N1526</b>	512 MB Memory

### SUPPLIES

<b>12A9615</b>	Cyan Toner, Regular, 5K Yield
<b>12A9620</b>	Magenta Toner, Regular, 5K Yield
<b>12A9625</b>	Yellow Toner, Regular, 5K Yield
<b>12A9635</b>	Cyan Toner, Use and Return, 5K Yield
<b>12A9640</b>	Magenta Toner, Use and Return, 5K Yield
<b>12A9645</b>	Yellow Toner, Use and Return, 5K Yield
<b>24B2069</b>	Black Toner, Use and Return, 4K Yield
<b>24B2070</b>	Black Toner, Regular, 4K Yield
<b>24B2080</b>	Photoconductor, Single Unit, 20K Yield

**Corporate Office:** 2 Musick, Irvine, California 92618-1631  
**East Coast:** 959 Route 46 East, 5th Floor, Parsippany, New Jersey 07054  
 Tel: 973/316-2700 Fax: 973/263-2393  
**Midwest:** 8770 W. Bryn Mawr Avenue, Suite 700, Chicago, Illinois 60631  
 Tel: 773/380-6000 Fax: 773/380-8077  
**South:** 4855 Peachtree Industrial Blvd., Suite 210, Norcross, Georgia 30092-3024  
 Tel: 770/209-8540 Fax: 770/209-8556  
**West Coast:** 142 Technology, Suite 150, Irvine, California 92618  
 Tel: 949/462-6262 Fax: 949/462-2700  
**Web Site:** www.copiers.toshiba.com or www.fax.toshiba.com  
 © 2007 Toshiba America Business Solutions, Inc., Electronic Imaging Division  
 e-studio220CP Spec/Inv. Code ES220CP2

Designs and specifications subject to change without notice. Actual specifications based on engine design and may vary according to usage and environment. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Toner yields are estimates, based on 5% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability.

AUTHORIZED TOSHIBA DEALER

**TOSHIBA**  
Leading Innovation >>>